

ZETA

4680UOO200P63 WT46

EAN 4031582307887
Order number 00830069



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ○ ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Zeta
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	600 kg
Load capacity at 6 km/h	480 kg
Load capacity Static	1200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	240 mm
Overall weight	2.871 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	200 mm
Tread width	46 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material fork	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Offset	55 mm
Swivel radius	155 mm
Swivel interference	310 mm

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

ZETA

4680UOO200P63 WT46

EAN 4031582307887
Order number 00830069



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

