

# LUMINA

AA20POI050L51-8 9011/9011

EAN 4031582317510



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                             |
|-----------------------------|-----------------------------|
| Product Name                | Lumina                      |
| Type                        | Swivel castor               |
| Standard                    | EN12528 - Furniture Castors |
| Load capacity at 3 km/h     | 40 kg                       |
| Electric Conductive         | No                          |
| Stainless                   | No                          |
| Load capacity Static        | 80 kg                       |
| Temperature range (Minimum) | -20 °C                      |
| Temperature range (Maximum) | 60 °C                       |
| Overall Height              | 56 mm                       |
| Overall width               | 55 mm                       |
| Overall weight              | 0.08 kg                     |

## HOUSING

|                     |                            |
|---------------------|----------------------------|
| Housing Material    | Polypropylene              |
| Fork shape          | Twin wheel housing, closed |
| Swivel Bearing      | Stem, swiveling            |
| Housing Color       | Graphite black (RAL9011)   |
| Offset              | 20 mm                      |
| Swivel radius       | 52 mm                      |
| Swivel interference | 104 mm                     |
| Dome diameter       | 0 mm                       |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polypropylene                  |
| Tread Material Mix    | Identical with wheel body      |
| Bearing               | Plain bearing with spacer tube |
| Axle                  | Riveted                        |
| Tread Color           | Graphite black (RAL9011)       |
| Wheel Color           | Graphite black (RAL9011)       |
| Threadguards          | Without threadguard            |
| Diameter              | 50 mm                          |
| Tread width           | 7 mm                           |
| Axle Hole Diameter    | 0 mm                           |
| Hub Length            | 0 mm                           |
| Body width            | 7 mm                           |
| Hardness of tread (D) | 65 Shore D                     |

## FITTING

|                    |                    |
|--------------------|--------------------|
| Fitting type       | Blind hole for B10 |
| Bolt hole diameter | 8 mm               |

# LUMINA

AA20POI050L51-8 9011/9011

EAN 4031582317510

Order number 00071497

**Product Drawings**



BETTER MOBILITY. BETTER LIFE.

