

COMPACTA

1430POI038P60-46X38

EAN 4031582336672
Order number 00032083



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Compacta
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	25 kg
Load capacity Static	50 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	50.5 mm
Overall width	32 mm
Overall weight	0.071 kg

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	38 mm
Tread width	16 mm
Body width	16 mm
Hardness of tread (D)	65 Shore D

HOUSING

Material fork	Steel sheet, light
Fork shape	Broad
Swivel bearing	One ball race
Colour	Blue passivated
Offset	13 mm
Swivel radius	32 mm
Swivel interference	64 mm
Dome diameter	32 mm

FITTING

Fitting type	Rectangular plate
Plate length	46 mm
Plate width	38 mm
Plate hole length (Maximum)	28 mm
Plate hole width (Maximum)	36 mm
Plate hole diameter	5.3 mm

PRODUCT INFORMATION

COMPACTA

1430POI038P60-46X38

EAN 4031582336672
Order number 00032083



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

