

DURATECH

TOP 080X60-Ø25 HL60

EAN 4031582331011
Broj porudžbine 00827802

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	80 mm
Širina omotac	60 mm
dimenzija rupa osovina	25 mm
dužina glavcine	60 mm
Širina tela	60 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6005

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	600 kg
Nosivost na 6 km/h	480 kg
Statički Nosivost	1200 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,441 kg

DURATECH

TOP 080X60-Ø25 HL60

EAN 4031582331011
Broj porudžbine 00827802



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

