

ALPHA

3478DRJ100P62

EAN 4031582410679



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	128 mm
Overall weight	0.638 kg

WHEEL

Body material	Sheet Steel
Tread material	Wound tread made of canvas and phenolic resin
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	100 mm
Tread width	30 mm
Hardness of tread (A)	85 Shore A

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad

FITTING

Fitting type	Rectangular plate
Plate length	103 mm
Plate width	85 mm
Plate hole length (Minimum)	77 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Maximum)	60 mm
Plate hole diameter	9 mm

ALPHA

3478DRJ100P62

EAN 4031582410679



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

