

# LEVINA

5371PJP125P50 7001/6032

EAN 4031582358742  
Order number 00036901



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                     |
|-----------------------------|-------------------------------------|
| Product name                | Levina                              |
| Housing type                | Swivel castor with directional lock |
| Standard                    | EN12530 - Devices Castors           |
| Load capacity at 3 km/h     | 100 kg                              |
| Load capacity Static        | 200 kg                              |
| Temperature range (Minimum) | -10 °C                              |
| Temperature range (Maximum) | 40 °C                               |
| Overall height              | 161 mm                              |
| Overall width               | 59 mm                               |
| Overall weight              | 0.609 kg                            |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread material        | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Wheel color           | Silver grey (RAL7001)  |
| Threadguards          | With threadguard       |
| Diameter              | 125 mm                 |
| Tread width           | 32 mm                  |
| Body width            | 32 mm                  |
| Hardness of tread (A) | 87 Shore A             |

## HOUSING

|                     |                       |
|---------------------|-----------------------|
| Material fork       | Polyamide             |
| Fork shape          | Slim                  |
| Swivel bearing      | Two ball races        |
| Colour              | Silver grey (RAL7001) |
| Offset              | 38 mm                 |
| Swivel radius       | 100.5 mm              |
| Swivel interference | 201 mm                |
| Dome diameter       | 59 mm                 |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 77 mm             |
| Plate width                 | 67 mm             |
| Plate hole length (Minimum) | 46.5 mm           |
| Plate hole length (Maximum) | 51.5 mm           |
| Plate hole width (Minimum)  | 56 mm             |
| Plate hole width (Maximum)  | 61.5 mm           |
| Plate hole diameter         | 8.5 mm            |

# LEVINA


5371PJP125P50 7001/6032

EAN 4031582358742  
Order number 00036901



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS



Universal  
Design  
Award



Deutscher  
Designer  
Club