

ALPHA STAINLESS

8478IDG100P62 TREAD-1023

EAN 4031582347098
Order number 00037682



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ●
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	176.37 lb
Load capacity Static	352.74 lb
Temperature range (Minimum)	-22 °F
Temperature range (Maximum)	482 °F
Overall height	5.04 in
Overall width	3.35 in
Overall weight	1.35 lb

WHEEL

Body material	Aluminum
Tread material	Damping, heat resistant
Bearing	Dry bearing bush
Axle	Screwed with nut
Wheel color	Metallic
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.38 in
Body width	1.38 in
Hardness of tread (A)	75 Shore A

HOUSING

Material	Stainless steel, heavy
Fork shape	Broad
Color	Stainless steel
Stainless	✓

FITTING

Fitting type	Rectangular plate
Plate length	3.94 in
Plate width	3.35 in
Plate hole length (Minimum)	3.03 in
Plate hole length (Maximum)	2.36 in
Plate hole width (Minimum)	3.03 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.35 in

ALPHA STAINLESS

8478IDG100P62 TREAD-1023

EAN 4031582347098
Order number 00037682



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

