

AGILA TWIN

2970PIP075P30-10

EAN 4031582362282



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda	Agila twin
Tip	Okretanje Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	80 kg
Statički Nosivost	160 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	99 mm
Ukupna težina	0,541 kg

TOCAK

Materijal za telo	polipropilen
	mekan
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	75 mm
Širina omotac	25 mm
Teškoća gazećeg omotac (A)	75 Šor A

KUCISTE

Materijal	Čelični list, srednji
oblik viljuska	kuciste za dva Tocak
okretni lezaj	Dve lopte
ofset	31,4 mm
okretni radijus	68,9 mm
Otpor okretanju	137,8 mm

PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	10 mm

AGILA TWIN

2970PIP075P30-10

EAN 4031582362282



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

