

DURATECH

MOP 300x80-Ø50 HL90

EAN 4031582320091



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, super heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	11.81 in
Tread width	3.15 in
Axle hole diameter	1.97 in
Hub length	3.54 in
Body width	3.15 in
Hardness of tread (D)	75 Shore D
Bearing type	6310

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	17196.04 lb
Load capacity at 3.7 mph	14330.03 lb
Electric conductive	no
Stainless	no
Load capacity Static	28660.06 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	18.34 lb

DURATECH

MOP 300x80-Ø50 HL90


EAN 4031582320091

Order number 00830851

Product Drawings



BETTER MOBILITY. BETTER LIFE.




PRODUCT INFORMATION

DURATECH

MOP 300x80-Ø50 HL90

EAN 4031582320091

Order number 00830651



BETTER MOBILITY. BETTER LIFE.