

PLATE

P41-38X38 / 10 DRILLED PLATE

EAN 4031582411928



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Corrosion resistance ●●●○○

CORE ATTRIBUTES

Product name	Plate
Type	Accessory
Load capacity at 3 km/h	60 kg
Load capacity Static	120 kg
Overall height	10 mm
Overall weight	0.053 kg

FITTING

Fitting type	Square plate
Plate length	38 mm
Plate width	38 mm
Plate hole length (Maximum)	27 mm
Plate hole width (Maximum)	27 mm
Plate hole diameter	5 mm