

PRODUCT INFORMATION

DURATECH HEAT

BOG 080X35 HL45,5 ASM.

EAN 4031582317695
Order number 00035369



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

HOUSING

Stainless	✓
-----------	---

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Duratech heat
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	220.46 lb
Load capacity Static	440.92 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	536 °F
Overall weight	0.46 lb

WHEEL

Body material	Plastic thermoset, heat-resistant
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Wheel color	Black
Diameter	3.15 in
Tread width	1.38 in
Axle hole diameter	0.31 in
Hub length	1.79 in
Body width	1.38 in
Hardness of tread (D)	90 Shore D

DURATECH HEAT

BOG 080X35 HL45,5 ASM.

EAN 4031582317695
Order number 00035369



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

