

# LINEA

5940XSC100P30-13 RAL9002

EAN 4031582352467



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	●●●●●
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●●○

## CORE ATTRIBUTES

Product name	Linea
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	120 kg
Electric conductive	✓
Stainless	✓
Load capacity Static	240 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	118 mm
Overall width	82 mm
Overall weight	0.618 kg

## WHEEL

Body material	Polyamide, electric conductive
Tread material	Polyurethane, injected, electric-conductive
Bearing	Precision ball bearing, stainless
Tread color	Slate grey (RAL7015)
Wheel color	Slate grey (RAL7015)
Threadguards	With threadguard
Diameter	100 mm
Tread width	20 mm
Body width	20 mm
Hardness of tread (A)	92 Shore A

## HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Colour	Grey white (RAL9002)
Offset	32 mm
Swivel radius	90 mm
Swivel interference	180 mm
Dome diameter	52 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm



# LINEA

5940XSC100P30-13 RAL9002


EAN 4031582352467



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---



Deutscher  
Designer  
Club



Interzum  
Award



IF  
Design  
Award