

# KAPPA LOAD

9651IEP250P63

EAN 4031582471922



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance ● ● ● ○ ○

Attrition ● ● ● ○ ○

Corrosion resistance ● ● ● ○ ○

## CORE ATTRIBUTES

|                             |                                     |
|-----------------------------|-------------------------------------|
| Product name                | Kappa load                          |
| Housing type                | Swivel castor with directional lock |
| Load capacity at 4 km/h     | 500 kg                              |
| Load capacity Static        | 1000 kg                             |
| Temperature range (Minimum) | -20 °C                              |
| Temperature range (Maximum) | 80 °C                               |
| Overall height              | 305 mm                              |

## WHEEL

|                       |                                 |
|-----------------------|---------------------------------|
| Body material         | Aluminium                       |
| Tread material        | Elastic tire, black, vulcanized |
| Bearing               | Precision ball bearing          |
| Axle                  | Screwed with nut                |
| Threadguards          | Without threadguard             |
| Diameter              | 250 mm                          |
| Tread width           | 50 mm                           |
| Hardness of tread (A) | 68 Shore A                      |

## HOUSING

|                     |                                        |
|---------------------|----------------------------------------|
| Material fork       | Iron forged, heavy                     |
| Fork shape          | Broad, reinforced                      |
| Swivel bearing      | Deep-groove ball thrust roller bearing |
| Offset              | 61 mm                                  |
| Swivel radius       | 199 mm                                 |
| Swivel interference | 398 mm                                 |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 135 mm            |
| Plate width                 | 110 mm            |
| Plate hole length (Maximum) | 105 mm            |
| Plate hole width (Minimum)  | 75 mm             |
| Plate hole width (Maximum)  | 80 mm             |
| Plate hole diameter         | 11 mm             |

# KAPPA LOAD

96511EP250P63

EAN 4031582471922



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

