PRODUCT INFORMATION

ALPHA SMART STAINLESS

8377BOG100P30-13

EAN 4031582494198

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●○○
Attrition	●●●●●
Corrosion Resistance	●●●●●

CORE ATTRIBUTES

Product Name	Alpha smart stainless
Type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	125 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	250 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	280 °C
Overall Height	128 mm
Overall weight	0.72 kg

HOUSING

Housing Material	Stainless steel, heavy
Fork shape	Slim
Swivel Bearing	Two ball races
Offset	41 mm
Swivel radius	91 mm
Swivel interference	182 mm

WHEEL

Body material	Plastic thermoset, heat-resistant
Tread Material Mix	Identical with wheel body
Bearing	Dry bearing bush
Axle	Screwed with nut
Diameter	100 mm
Tread width	35 mm
Hardness of tread (D)	85 Shore D

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

© Copyright 2026 TENTE International GmbH