

# GALEA STAINLESS

5088PJM125R05-22X40

EAN 4031582336535



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●●●

## OSNOVNI ATRIBUTI

|                                |                           |
|--------------------------------|---------------------------|
| Naziv proizvoda                | Galea stainless           |
| Tip                            | Fiksni Tocak              |
| Standard                       | EN12530 - Kastori uređaja |
| Nosivost na 3 km/h             | 100 kg                    |
| nerdjajuci                     | ✓                         |
| Statički Nosivost              | 200 kg                    |
| Temperaturni opseg (Minimalno) | -20 °C                    |
| Opseg temperature (maksimalni) | 60 °C                     |
| Sveukupna visina               | 162 mm                    |

## TOCAK

|                            |                          |
|----------------------------|--------------------------|
| Materijal za telo          | polipropilen             |
| materijal omotaca          | Termoplastična guma      |
| Nošenje                    | klizni lezaj, nerdjajuci |
| stitnici omotaca           | Sa threadguard           |
| Prečnik                    | 125 mm                   |
| Širina omotac              | 30 mm                    |
| Teškoća gazećeg omotac (A) | 87 Šora A                |

## KUCISTE

|                 |           |
|-----------------|-----------|
| Materijal       | poliamid  |
| oblik viljuska  | Zatvoreno |
| ofset           | 40 mm     |
| okretni radijus | 102,5 mm  |
| Otpor okretanju | 205 mm    |

## PRILAGOĐAVANJE

|               |                 |
|---------------|-----------------|
| Tip uklapanja | stablo, okrugla |
| Prečnik sraf  | 22 mm           |
| Dužina sraf   | 40 mm           |

# GALEA STAINLESS

5088PJM125R05-22X40

EAN 4031582336535



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---

