

STYLEA

5920UOI065B10-11X20/10D23 9011/9011

EAN 4031582310863
Order number 00074435



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Stylea
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	110.23 lb
Load capacity Static	220.46 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.68 in
Overall width	1.69 in
Overall weight	0.28 lb

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	Graphite black (RAL9011)
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	2.56 in
Tread width	0.31 in
Axle hole diameter	0 in
Hub length	0 in
Body width	0.31 in
Hardness of tread (D)	65 Shore D

HOUSING

Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Color	Graphite black (RAL9011)
Offset	0.98 in
Swivel radius	2.09 in
Swivel interference	4.17 in
Dome diameter	0.91 in

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.43 in
Stem length	0.79 in

PRODUCT INFORMATION

STYLEA

5920UOI065B10-11X20/10D23 9011/9011

EAN 4031582310863
Order number 00074435



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

