

STEM

S70-8X25 / 10

EAN 4031582424669



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Stem
Type	Accessory
Load capacity at 3 km/h	50 kg
Load capacity Static	100 kg
Overall height	6 mm
Overall weight	0.03 kg

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	8 mm
Stem length	25 mm