

# ELASTECH

UER 125x40-Ø12

EAN 4031582323306



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Elastech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 250 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 500 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 80 °C                         |
| Overall weight              | 0.4 kg                        |

## WHEEL

|                       |                                 |
|-----------------------|---------------------------------|
| Tread hardness        | soft                            |
| Body material         | Polyamide                       |
| Tread Material Mix    | Elastic tire, black, vulcanized |
| Bearing               | Roller bearing                  |
| Wheel Color           | Silver grey (RAL7001)           |
| Threadguards          | Without threadguard             |
| Diameter              | 125 mm                          |
| Tread width           | 40 mm                           |
| Axle Hole Diameter    | 12 mm                           |
| Hub Length            | 44 mm                           |
| Body width            | 40 mm                           |
| Hardness of tread (A) | 63 Shore A                      |

