PRODUCT INFORMATION

ELASTECH

UER 125x40-Ø12

EAN 4031582323306



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●●○
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	250 kg
Electric Conductive	No
Stainless	No
Load capacity Static	500 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.4 kg

WHEEL

Tread hardness	soft
Body material	Polyamide
Tread Material Mix	Elastic tire, black, vulcanized
Bearing	Roller bearing
Wheel Color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	125 mm
Tread width	40 mm
Axle Hole Diameter	12 mm
Hub Length	44 mm
Body width	40 mm
Hardness of tread (A)	63 Shore A

© Copyright 2026 TENTE International GmbH


ELASTECH

UER 125x40-Ø12

EAN 4031582323306

Order number 00030962

Product Drawings



© Copyright 2026 TENTE International GmbH