

# ELASTECH

IEP180X50-Ø20 HL54

EAN 4031582456769



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Aluminium
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	180 mm
Tread width	50 mm
Axle hole diameter	20 mm
Hub length	54 mm
Hardness of tread (A)	68 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	400 kg
Load capacity at 6 km/h	320 kg
Load capacity Static	800 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	1.405 kg

# ELASTECH

IEP180X50-Ø20 HL54

EAN 4031582456769



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

