

MONO

5025PJH080L51-10 ~9006/9011/9011/9011

EAN 4031582317138



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-------------|
| Roll Performance | ● ● ● ● ○ ○ |
| Movement Noise | ● ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|--------------------------------|
| Product Name | Mono |
| Type | Swivel castor with wheel brake |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 3 km/h | 70 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 140 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall Height | 104 mm |
| Overall width | 0 mm |
| Overall weight | 0.14 kg |

HOUSING

| | |
|---------------------|---------------------------|
| Housing Material | Polyamide |
| Fork shape | Closed |
| Swivel Bearing | Stem, swiveling |
| Housing Color | White aluminium (RAL9006) |
| Offset | 34 mm |
| Swivel radius | 105 mm |
| Swivel interference | 210 mm |
| Dome diameter | 0 mm |

WHEEL

| | |
|-----------------------|--------------------------|
| Body material | Polypropylene |
| Tread Material Mix | Thermoplastic rubber |
| Bearing | Plain bearing |
| Tread Color | Graphite black (RAL9011) |
| Wheel Color | Graphite black (RAL9011) |
| Threadguards | With threadguard |
| Diameter | 80 mm |
| Tread width | 24 mm |
| Axle Hole Diameter | 0 mm |
| Hub Length | 0 mm |
| Body width | 24 mm |
| Hardness of tread (A) | 90 Shore A |

FITTING

| | |
|--------------------|--------------------|
| Fitting type | Blind hole for B10 |
| Bolt hole diameter | 10 mm |

MONO

5025PJH080L51-10 ~9006/9011/9011/9011

EAN 4031582317138



BETTER MOBILITY. BETTER LIFE.

Product Drawings

