PRODUCT INFORMATION

MONO

5025PJH080L51-10 ~9006/9011/9011/9011

EAN 4031582317138



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●○○
Corrosion Resistance	●●●●○

CORE ATTRIBUTES

Product Name	Mono
Type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	70 kg
Electric Conductive	No
Stainless	No
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	104 mm
Overall width	0 mm
Overall weight	0.14 kg

HOUSING

Housing Material	Polyamide
Fork shape	Closed
Swivel Bearing	Stem, swiveling
Housing Color	White aluminium (RAL9006)
Offset	34 mm
Swivel radius	105 mm
Swivel interference	210 mm
Dome diameter	0 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing
Tread Color	Graphite black (RAL9011)
Wheel Color	Graphite black (RAL9011)
Threadguards	With threadguard
Diameter	80 mm
Tread width	24 mm
Axle Hole Diameter	0 mm
Hub Length	0 mm
Body width	24 mm
Hardness of tread (A)	90 Shore A

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

© Copyright 2026 TENTE International GmbH


MONO

5025PJH080L51-10 ~9006/9011/9011/9011

EAN 4031582317138

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH