

ALPHA

3477UER200P30-13

EAN 4031582305852



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ○ ○
Corrosion resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Type	Swivel caster with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	440.92 lb
Electric conductive	no
Stainless	no
Load capacity Static	881.85 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall height	9.25 in
Overall weight	6 lb

HOUSING

Housing Material	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Housing Color	Blue passivated
Offset	2.17 in
Swivel radius	6.54 in
Swivel interference	13.07 in

WHEEL

Tread hardness	soft
Body material	Polyamide
Tread material	Elastic tire, black, vulcanized
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	7.87 in
Tread width	1.81 in
Hardness of tread (A)	64 Shore A

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in

ALPHA

3477UER200P30-13

EAN 4031582305852



BETTER MOBILITY. BETTER LIFE.

Product Drawings

