

PRODUCT INFORMATION

NOVATECH

ITP250x50-Ø25-SH80A

EAN 4031582428629



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL


|                       |                        |
|-----------------------|------------------------|
| Body material         | Aluminium              |
| Tread Material Mix    | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Threadguards          | Without threadguard    |
| Diameter              | 250 mm                 |
| Tread width           | 50 mm                  |
| Axle Hole Diameter    | 25 mm                  |
| Hub Length            | 60 mm                  |
| Hardness of tread (A) | 80 Shore A             |

PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Novatech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 800 kg                        |
| Load capacity at 6 km/h     | 640 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 1600 kg                       |
| Temperature range (Minimum) | -10 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall weight              | 2.15 kg                       |




PRODUCT INFORMATION

**NOVATECH**

ITP250x50-Ø25-SH80A

EAN 4031582428629



BETTER MOBILITY. BETTER LIFE.