PRODUCT INFORMATION

OMIKRON TWIN

9958FTP200P65

EAN 4031582316964




Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●●○

CORE ATTRIBUTES

Product Name	Omikron twin
Type	Fixed castor
Standard	similar EN12532 - Transport Equipment
Load capacity at 4 km/h	2500 kg
Load capacity at 6 km/h	2000 kg
Electric Conductive	No
Stainless	No
Load capacity Static	3750 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall Height	275 mm
Overall width	154 mm
Overall weight	15.77 kg

HOUSING

Housing Material	Iron forged, heavy
Fork shape	Twin wheel housing
Housing Color	Transparent coating
Lubrication nipple	1
Dome diameter	160 mm

WHEEL

Body material	Cast iron
Tread Material Mix	PUR casted premium
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel Color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	200 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Medium rectangular heavy-duty plate
Plate length	200 mm
Plate width	160 mm
Plate hole length (Maximum)	120 mm
Plate hole width (Maximum)	160 mm
Plate hole diameter	15 mm

© Copyright 2026 TENTE International GmbH


OMIKRON TWIN


9958FTP200P65


EAN 4031582316964

Order number 00801882

Product Drawings







© Copyright 2026 TENTE International GmbH