

# DURATECH

TOP 080X74-Ø20 HL80

EAN 4031582331028  
Broj porudžbine 00829536

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	80 mm
Širina omotac	74 mm
dimenzija rupa osovina	20 mm
dužina glavcine	80 mm
Širina tela	74 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6204ZV

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	700 kg
Nosivost na 6 km/h	560 kg
Statički Nosivost	1400 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,449 kg

# DURATECH

TOP 080X74-Ø20 HL80

EAN 4031582331028  
Broj porudžbine 00829536



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

