

# COMPACTA

1530PJO040P30

EAN 4031582425352



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## HOUSING

Material fork	Steel sheet, light
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	One ball race
Offset	19 mm
Swivel radius	39 mm
Swivel interference	78 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	8 mm

## CORE ATTRIBUTES

Product name	Compacta
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	20 kg
Load capacity Static	40 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	52 mm
Overall weight	0.06 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Axle	Riveted
Threadguards	Without threadguard
Diameter	40 mm
Tread width	23 mm
Hardness of tread (A)	87 Shore A