

# DURATECH HEAT

WOG 075X25 HL31,8 BLACK

EAN 4031582382891  
Order number 00039564



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Thermoplastic synthetics, heat resistant
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Wheel color	Black
Diameter	2.95 in
Tread width	0.98 in
Axle hole diameter	0.31 in
Hub length	1.25 in
Body width	0.98 in
Hardness of tread (D)	80 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Duratech heat
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	110.23 lb
Stainless	✓
Load capacity Static	220.46 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	273.2 °F
Overall weight	0.19 lb

# DURATECH HEAT

WOG 075X25 HL31,8 BLACK

EAN 4031582382891  
Order number 00039564



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

