

# DURATECH SILENT

HUR100x36-Ø12 HL44

EAN 4031582452877



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Duratech silent               |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 160 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 320 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall weight              | 0.4 kg                        |

## WHEEL

|                       |                          |
|-----------------------|--------------------------|
| Body material         | Damping, hybrid material |
| Tread Material Mix    | Polyamide                |
| Bearing               | Roller bearing           |
| Threadguards          | Without threadguard      |
| Diameter              | 100 mm                   |
| Tread width           | 36 mm                    |
| Axle Hole Diameter    | 12 mm                    |
| Hub Length            | 44 mm                    |
| Hardness of tread (D) | 75 Shore D               |

# DURATECH SILENT

HUR100x36-Ø12 HL44

EAN 4031582452877



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

---

