

NOVATECH

FTP 160X50-Ø20 HL60

EAN 4031582329551
Broj porudžbine 00801166

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Ливено Гвожђе
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	160 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavčine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	1100 kg
Nosivost na 6 km/h	900 kg
Statički Nosivost	1800 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	2,62 kg

NOVATECH

FTP 160X50-Ø20 HL60

EAN 4031582329551
Broj porudžbine 00801166



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

