

# ZETA

4681ICP160P63-75A

EAN 4031582478068



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Zeta
Type	Swivel castor with directional lock
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	550 kg
Load capacity at 6 km/h	440 kg
Load capacity Static	1100 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	70 °C
Overall height	200 mm
Overall weight	3.274 kg

## WHEEL

Body material	Aluminium
Tread hardness	soft
Tread material	Ultratech Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	160 mm
Tread width	50 mm
Hardness of tread (A)	75 Shore A

## HOUSING

Material fork	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Offset	55 mm
Swivel radius	135 mm
Swivel interference	270 mm

## FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

# ZETA

4681ICP160P63-75A

EAN 4031582478068



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

