

PRODUCT INFORMATION

NOVATECH

ITP100x40-Ø20 HL40

EAN 4031582437607



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

|                             |                              |
|-----------------------------|------------------------------|
| Product Name                | Novatech                     |
| Type                        | Wheel                        |
| Standard                    | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h     | 300 kg                       |
| Electric Conductive         | No                           |
| Stainless                   | No                           |
| Load capacity Static        | 600 kg                       |
| Temperature range (Minimum) | -20 °C                       |
| Temperature range (Maximum) | 60 °C                        |
| Overall weight              | 0.47 kg                      |

WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Aluminium              |
| Tread Material Mix    | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Threadguards          | Without threadguard    |
| Diameter              | 100 mm                 |
| Tread width           | 40 mm                  |
| Axle Hole Diameter    | 20 mm                  |
| Hub Length            | 40 mm                  |
| Hardness of tread (A) | 92 Shore A             |

## Product Drawings

---

