

STORA

2875ZIP125P72 GAUCHE TFR

EAN 4031582386530



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Stora
Type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	161 mm
Overall weight	1.071 kg

WHEEL

Body material	Flanged wheel
Tread material	Solid rubber, non-marking
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Hardness of tread (A)	80 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Special Function
Swivel bearing	Two ball races
Offset	43 mm
Swivel radius	105.5 mm
Swivel interference	211 mm

FITTING

Fitting type	Vertical flange
--------------	-----------------

ADDITIONAL INFORMATION

Designed for the following palletsize: track width: approx. 2,75 mm, groove width: approx. 5,7 mm, groove depth: > 10 mm.

PRODUCT INFORMATION

STORA

2875ZIP125P72 GAUCHE TFR

EAN 4031582386530



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

