

COMPACTA

1438PVH065P60-75x60

EAN 3700001796762



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Compacta
Type	Fixed castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	85 mm
Overall weight	0.14 kg

HOUSING

Housing Material	Steel sheet, light
Fork shape	Broad
Housing Color	Blue passivated

WHEEL

Body material	Polypropylene
Tread Material Mix	Solid rubber, black
Bearing	Plain bearing
Axle	Riveted
Threadguards	With threadguard
Diameter	65 mm
Tread width	25 mm
Hardness of tread (A)	85 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	75 mm
Plate width	60 mm
Plate hole length (Maximum)	55 mm
Plate hole width (Maximum)	40 mm
Plate hole diameter	7 mm