

DELTA

3648ITP125P63 cv

EAN 4031582366419



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Delta
Type	Fixed caster
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1102.31 lb
Load capacity at 3.7 mph	881.85 lb
Electric conductive	no
Stainless	no
Load capacity Static	2204.62 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall height	7.01 in
Overall width	4.53 in
Overall weight	3.74 lb

HOUSING

Housing Material	Steel sheet, heavy
Fork shape	Broad, reinforced
Housing Color	Blue passivated
Dome diameter	4.53 in

WHEEL

Tread profile	convex
Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.53 in
Plate hole length (Minimum)	2.95 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	4.13 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

DELTA

3648ITP125P63 cv

EAN 4031582366419

Order number 00837568
Product Drawings



BETTER MOBILITY. BETTER LIFE.

