

LUMINA

A520POI035L51- 8

EAN 4031582443974



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Lumina
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	44.09 lb
Load capacity Static	88.18 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	1.54 in
Overall width	1.5 in
Overall weight	0.05 lb

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.38 in
Tread width	0.31 in
Hardness of tread (D)	65 Shore D

HOUSING

Material	Polypropylene
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	Stem, swiveling
Swivel radius	1.32 in
Swivel interference	2.64 in

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.24 in

PRODUCT INFORMATION

LUMINA

A520POI035L51- 8

EAN 4031582443974



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

