

AGILA

2470PIP100P30-11

EAN 4031582361261
Broj porudžbine 00038838

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Agila
Tip kućišta	Okretanje Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	80 kg
Statički Nosivost	160 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	135 mm
Ukupna težina	0,615 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	100 mm
Širina omotac	32 mm
Teškoća gazećeg omotac (A)	75 Šor A

KUCISTE

Materijal	Čelični list, srednji
oblik viljusk	siroko
okretni lezaj	Dve lopte
ofset	38 mm
okretni radijus	88 mm
Otpor okretanju	176 mm

PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	11 mm
Savet	Kastori se mogu montirati standardnim vijcima bilo koje dužine.

AGILA

2470PIP100P30-11

EAN 4031582361261
Broj porudžbine 00038838



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

