PRODUCT INFORMATION

AGILA

2478PJI050P41-55

EAN 4031582030013



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●●○
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Agila
Type	Fixed castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	69 mm
Overall width	35 mm
Overall weight	0.09 kg

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Housing Color	Blue passivated
Dome diameter	27 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Wheel Color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	50 mm
Tread width	19 mm
Body width	19 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Square plate
Plate length	55 mm
Plate width	55 mm
Plate hole length (Minimum)	38.5 mm
Plate hole length (Maximum)	44 mm
Plate hole width (Minimum)	38.5 mm
Plate hole width (Maximum)	44 mm
Plate hole diameter	6.3 mm

© Copyright 2026 TENTE International GmbH


AGILA


2478PJI050P41-55


EAN 4031582030013

Order number 00003898

Product Drawings







© Copyright 2026 TENTE International GmbH