

ALPHA STAINLESS

8470UAD100P30-11 RED

EAN 4031582370072



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ● ● ○

otpornost na rdju ● ● ● ● ●

OSNOVNI ATRIBUTI

Naziv proizvoda	Alpha stainless
Tip kućišta	Okretanje Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	150 kg
Statički Nosivost	300 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Sveukupna visina	128 mm
Ukupna težina	0,801 kg

TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	kotrljajući lezaj, nerdjajući
osovina	Završena sa navrtkom
Prečnik	100 mm
Širina omotac	32 mm
Teškoća gazećeg omotac (D)	42 Šor D

KUCISTE

Materijal	nerdjajući čelik, težak
oblik viljaska	siroko
okretni lezaj	Dve lopte
ofset	41 mm
okretni radijus	91 mm
Otpor okretanju	182 mm
nerdjajući	✓

PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	11 mm

ALPHA STAINLESS

8470UAD100P30-11 RED

EAN 4031582370072



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

