

# AGILA

2478PIO150P50

EAN 4031582362213



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Agila                     |
| Housing type                | Fixed castor              |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 1.8 mph    | 176.37 lb                 |
| Load capacity Static        | 352.74 lb                 |
| Temperature range (Minimum) | -4 °F                     |
| Temperature range (Maximum) | 140 °F                    |
| Overall height              | 7.28 in                   |
| Overall weight              | 1.52 lb                   |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polypropylene             |
| Tread material        | Solid rubber, non-marking |
| Bearing               | Plain bearing             |
| Threadguards          | Without threadguard       |
| Diameter              | 5.91 in                   |
| Tread width           | 1.26 in                   |
| Hardness of tread (A) | 80 Shore A                |

## HOUSING

|            |                     |
|------------|---------------------|
| Material   | Steel sheet, medium |
| Fork shape | Broad               |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 3.03 in           |
| Plate width                 | 2.64 in           |
| Plate hole length (Minimum) | 2.2 in            |
| Plate hole length (Maximum) | 2.42 in           |
| Plate hole width (Minimum)  | 1.83 in           |
| Plate hole width (Maximum)  | 2.03 in           |
| Plate hole diameter         | 0.33 in           |

# AGILA

2478PIO150P50

EAN 4031582362213



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

