

PURETECH

DIK 150X32-Ø8,1

EAN 4031582070170
Broj porudžbine 00000163

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ● ○

Ishrana ● ● ● ○ ○

otpornost na rdju ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	100 kg
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	0,896 kg

TOCAK

Materijal za telo	Čelik lista
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	konusi lezaj
Boja Tocak	plavo cinkovano
stitnici omotaca	Sa threadguard
Prečnik	150 mm
Širina omotac	32 mm
dimenzija rupa osovina	8 mm
duzina glavcine	36 mm
Širina tela	32 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PURETECH

DIK 150X32-Ø8,1

EAN 4031582070170
Broj porudžbine 00000163



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

