

PRODUCT INFORMATION

BASETECH

POO3.5x1.25-Ø0.5 HL 40

EAN 4031582436099



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ● ● ●
Corrosion resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Basetech
Type	Wheel
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 1.8 mph	275.58 lb
Electric conductive	no
Stainless	no
Load capacity Static	551.16 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	3.5 in
Tread width	1.25 in
Axle hole diameter	0.48 in
Hub length	1.57 in
Hardness of tread (D)	66 Shore D

BASETECH

POO3.5x1.25-Ø0.5 HL 40

EAN 4031582436099



BETTER MOBILITY. BETTER LIFE.

Product Drawings

