

BASETECH

POR080X30-Ø12 WHITE TFR

EAN 4031582390582



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	80 mm
Tread width	30 mm
Axle hole diameter	12 mm
Hub length	44 mm
Hardness of tread (D)	69 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Basetech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.1 kg

BASETECH

POR080X30-Ø12 WHITE TFR

EAN 4031582390582



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

