

MAXTECH

UAD160X40-Ø25 TFR

EAN 4031582395334



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Roller bearing, stainless
Diameter	6.3 in
Tread width	1.57 in
Axle hole diameter	0.79 in
Hub length	2.28 in
Hardness of tread (D)	60 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	771.62 lb
Load capacity Static	1543.23 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall height	0 in

MAXTECH

UAD160X40-Ø25 TFR

EAN 4031582395334



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

