

PRODUCT INFORMATION

GLIDE

A229Y0I050B10-11X20/10 9011/1016

EAN 4031582319613
Order number 00075112



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Glide
Housing type	Customized solution
Electric conductive	✓
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	33 mm
Overall width	50 mm
Overall weight	0.065 kg

WHEEL

Body material	Polypropylene, electric conductive
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	50 mm
Hardness of tread (D)	65 Shore D



BETTER MOBILITY. BETTER LIFE.

HOUSING

Material	Polypropylene
Fork shape	Straight
Swivel bearing	Stem, swiveling
Colour	Graphite black (RAL9011)
Dome diameter	38 mm
Collar diameter	50 mm

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	11 mm
Stem length	20 mm

PRODUCT INFORMATION

GLIDE

A229YOI050B10-11X20/10 9011/1016

EAN 4031582319613
Order number 00075112



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

