

# AGILA

2478DIK125P50

EAN 4031582302363



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product Name                | Agila                     |
| Type                        | Fixed castor              |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 100 kg                    |
| Electric Conductive         | No                        |
| Stainless                   | No                        |
| Load capacity Static        | 200 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 80 °C                     |
| Overall Height              | 160 mm                    |
| Overall width               | 60 mm                     |
| Overall weight              | 1 kg                      |

## HOUSING

|                  |                     |
|------------------|---------------------|
| Housing Material | Steel sheet, medium |
| Fork shape       | Broad               |
| Housing Color    | Blue passivated     |
| Dome diameter    | 60 mm               |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Sheet Steel               |
| Tread Material Mix    | Solid rubber, non-marking |
| Bearing               | Cone ball bearing         |
| Wheel Color           | Blue passivated           |
| Threadguards          | With threadguard          |
| Diameter              | 125 mm                    |
| Tread width           | 32 mm                     |
| Body width            | 32 mm                     |
| Hardness of tread (A) | 80 Shore A                |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 77 mm             |
| Plate width                 | 67 mm             |
| Plate hole length (Minimum) | 46.5 mm           |
| Plate hole length (Maximum) | 51.5 mm           |
| Plate hole width (Minimum)  | 56 mm             |
| Plate hole width (Maximum)  | 61.5 mm           |
| Plate hole diameter         | 8.5 mm            |

# AGILA

2478DIK125P50

EAN 4031582302363

Order number 00006269

Product Drawings



BETTER MOBILITY. BETTER LIFE.

