

COMPACTA

2198PII036P40-42

EAN 4031582332568



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Compacta
Type	Fixed caster
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	66.14 lb
Electric conductive	no
Stainless	no
Load capacity Static	132.28 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	122 °F
Overall height	1.89 in
Overall weight	0.13 lb

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Angular
Swivel radius	1.26 in

WHEEL

Tread hardness	soft
Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.5 in
Tread width	0.59 in
Hardness of tread (A)	75 Shore A

FITTING

Fitting type	Square plate
Plate length	2.17 in
Plate width	0.98 in
Plate hole length (Maximum)	1.77 in
Plate hole width (Maximum)	1.77 in
Plate hole diameter	0.24 in

COMPACTA

2198PII036P40-42

EAN 4031582332568



BETTER MOBILITY. BETTER LIFE.

Product Drawings

