

SUPRATECH

PJR 125X32-Ø12

EAN 4031582320534
Broj porudžbine 00030821

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Termoplastična guma
Nošenje	kotrljajući lezaj
Boja Tocak	Srebrna siva (RAL7001)
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	32 mm
dimenzija rupa osovina	12 mm
dužina glavcine	34,9 mm
Širina tela	32 mm
Teškoća gazećeg omotac (A)	87 Šora A

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Supratech
Tip	Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	100 kg
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,239 kg

SUPRATECH

PJR 125X32-Ø12

EAN 4031582320534
Broj porudžbine 00030821



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

