

# LUMINA

A520POI050B10-11X20/10D38 9011 SP

EAN 4031582317275



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                 |
|-----------------------------|---------------------------------|
| Product Name                | Lumina                          |
| Type                        | Swivel castor                   |
| Standard                    | EN12529 - Swivel Chairs Castors |
| Load capacity at 3 km/h     | 40 kg                           |
| Electric Conductive         | No                              |
| Stainless                   | No                              |
| Load capacity Static        | 80 kg                           |
| Temperature range (Minimum) | -20 °C                          |
| Temperature range (Maximum) | 60 °C                           |
| Overall Height              | 61 mm                           |
| Overall width               | 55 mm                           |
| Overall weight              | 0.09 kg                         |

## HOUSING

|                     |                                       |
|---------------------|---------------------------------------|
| Housing Material    | Polypropylene                         |
| Fork shape          | Twin wheel housing, closed, with dome |
| Swivel Bearing      | Stem, swiveling                       |
| Housing Color       | Graphite black (RAL9011)              |
| Offset              | 20 mm                                 |
| Swivel radius       | 52 mm                                 |
| Swivel interference | 104 mm                                |
| Dome diameter       | 38 mm                                 |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polypropylene                  |
| Tread Material Mix    | Identical with wheel body      |
| Bearing               | Plain bearing with spacer tube |
| Axle                  | Riveted                        |
| Tread Color           | Graphite black (RAL9011)       |
| Wheel Color           | Graphite black (RAL9011)       |
| Threadguards          | Without threadguard            |
| Diameter              | 50 mm                          |
| Tread width           | 8 mm                           |
| Axle Hole Diameter    | 0 mm                           |
| Hub Length            | 0 mm                           |
| Body width            | 8 mm                           |
| Hardness of tread (D) | 65 Shore D                     |

## FITTING

|               |                                  |
|---------------|----------------------------------|
| Fitting type  | Stem with grip ring, with collar |
| Stem diameter | 11 mm                            |
| Stem length   | 20 mm                            |

# LUMINA

A520POI050B10-11X20/10D38 9011 SP

EAN 4031582317275

Order number 00071168

**Product Drawings**



BETTER MOBILITY. BETTER LIFE.

