

PRODUCT INFORMATION

MAXTECH

PNR400x90-Ø10 HL129 yellow with axle

EAN 4031582438192



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread Material Mix	Polyurethane, foamed
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	400 mm
Tread width	90 mm
Axle Hole Diameter	10 mm
Hub Length	129 mm

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Load capacity at 3 km/h	145 kg
Electric Conductive	No
Stainless	No
Load capacity Static	290 kg
Overall weight	3 kg

MAXTECH

PNR400x90-Ø10 HL129 yellow with axle

EAN 4031582438192



BETTER MOBILITY. BETTER LIFE.

Product Drawings

